

www.cometsystem.com

# PRODUCT DESCRIPTION

The COMETEO radiation shield F8100 is used to protect the COMET air temperature, relative humidity and pressure sensors from thermal radiation and climatic influences. Mounting flange under the top cover allows easy mounting of the devices including the fixing of the cables.

## **DIMENSIONS**



#### RADIATION SHIELD MOUTING


The radiation shield place to a mast with diameter from 20 mm to 45 mm (i.e. satellite holder). The radiation shield is advisable to place at least 50 cm from the nearest wall of the building and at least 1.8 meters above the ground. For professional measurements are recommended the grassy places, which in a radius of 10 m has no obstacles (lawn should be continuously maintained).


# TRANSMITTERS AND MEASURING PROBES INSTALLATION


Remove the top cover by turning it counter-clockwise by 60° (see figure at

right). To install transmitters use the mounting holes in the upper flange of the shield (see pictures below). The probe on the cable place into the interior space by sliding it into flexible holders (the probe should be placed as low as possible to minimize the heating of the temperature and humidity sensors from the top part of the cover exposed to sunlight). The device fix with the attached M4x8 screws, the connection cables fasten using the attached cable ties. In conclusion, fasten the top cover to its turning clockwise.

We recommend you at first to insert the device into the radiation shield, then fasten the U-bolt bracket to the mast and after that consolidate the radiation shield using the attached two nuts M8.









T3319, T3511, T7311 T7411, T7511 T0213D, T3113D T3413D

P0132



The placement of the probe (T7311) into the shield ------



#### TECHNICAL SPECIFICATION

Temperature operating range: -30 to +80 °C Relative humidity operating range: 0 to 100 %RH Storage temperature range: -30 to +80 °C

Storage relative humidity range: 0 to 100 %RH (no condensation)

Weight: approximately 900 g

Material: ASA - UV stabilized, antistatic

# **CONTENT OF THE PACKAGE:**

the F8100 shield
the U-bolt bracket
the screw M4x8
the cable tie
the nut M8
1 pc
4 pcs
3 pcs
2 pcs

#### **END OF OPERATION**

The radiation shield dispose according to current legislation for dealing with electronic equipment.

### TECHNICAL SUPPORT AND SERVICE

Technical support and service is provided by distributor. For contact see warranty certificate. If needed, you can also use the discussion forum at <a href="http://www.forum.cometsystem.com/">http://www.forum.cometsystem.com/</a>.

WARNING	
---------	--

Installation, commissioning and maintenance may only be carried out by personnel with qualification by applicable regulations and standards.

© Copyright: COMET System, s.r.o.

It is prohibited to copy and make any changes in this manual, without explicit agreement of company COMET System, Ltd. All rights reserved.

COMET System, Ltd. makes constant development and improvement of their products. Manufacturer reserves the right to make technical changes to the device without previous notice. Misprints reserved.